

TRITICALE RECEIVAL STANDARDS – 2001/2002 SEASON REFERENCE CHART



Application

The following standards apply for the receipt of Triticale

Standard

1. **TRIT** = Triticale (No.1) Receival Standards
2. **TRIF** = Triticale (Feed) Receival Standards
3. For details regarding the receival standards for triticale refer to the AusBulk Ltd Commodity Classification Manual

Category		Code	TRIT	TRIF
Moisture content	Maximum %	MO	12.5	12.5
Test weight	Minimum kg/hl	TW	65	60
Screenings -below the screen	Maximum % (by weight)	SC	10	15
Unmillable material - above the screen	Maximum % (by volume)	SA	5	10
DEFECTIVE GRAINS Maximum % By 300 grain count				
Sprouted Grains		SP	2	No Limit
Insect damaged Grains		ID	2	4
Dark Fungal Staining		FS	15	50
Pink Fungal Staining		PF	5	5
Dry Green, Sappy and Frost Distorted grains		GS	2	No Limit

NOMINATED FOREIGN WEED SEEDS** Maximum seeds per ½ litre				
Type 1: Three Cornered Jack, Poppy, Parthenium Weed		S1	8	8
Type 2: Coriander, Wild Garlic, Ragweed, St Johns Wort		S2	NIL	NIL
Type 3a: Caltrop, Bathurst Burr, Cape Tulip		3A	2	2
Type 3b: Vetch		3B	4	4
Type 3c: Heliotrope		3C	8	8
Type 4: Cutleaf Mignonette, Skeleton Weed, Nightshades, Melilotus, Variegated Thistle		S4	20	20
Type 5: Knapweed, Salvation Jane		S5	40	40
Type 6: Colombus Grass, Johnson Grass, Saffron Thistle		S6	50	50
Type 7: Pulses, Corn, Sunflower, Safflower		S7	10	100
Type 8: Cereal Grains, Turnip Weed, Black Oats, Brome Grass, Lucerne Pods.		S8	150	400

Grain Insects, Rodents, Etc	Maximum per 1/2 litre		NIL	NIL
SNAILS: White Snail, White Italian Snail, Pointed Snail and Small Pointed Snail	Maximum per 1/2 litre	SN	1	5
ERGOT: Triticale Ergot	Maximum pieces per 1/2 litre	TE	1	1

** Nominated weed seeds in Triticale are equivalent to those for Wheat, with TRIT equivalent to GP1, and TRIF equivalent to FEED

For other weed seeds, refer to tolerances for Seed Contaminants in the Commodity Classification Manual