

Australian Bulk Alliance

A.B.N. 39 087 280 260

OAT RECEIVAL STANDARDS – 2002/2003 SEASON REFERENCE CHART



PARAMETER	BINNED GRADE		
	Code	Grade code	Goodman Fielder Oats
Test			UOAT
Variety	VR		ECHIDNA
Grain to be bright, sound, well filled and free from objectional material.			
Moisture	MO	max %	12.0%
Test weight	TW	min	52.0kg/hl
Screenings Below 1.85 mm screen	SC	Max % by weight	8.0%
Retention Above 2.10mm screen	RT	Min % by weight	80.0%
Admixture Foreign Material PLUS Unmillable Material	ADM	Max % by weight	3.0%
Foreign Material	TF	Max % by weight	2.0%
Weed Seeds			
Contaminating Seeds (Wild Oats, canola, thistle, vetch, sheep weed, lupins, peas, thornapple, wild turnip)	SW	Max % by weight	0.5%
Foreign Cereals (Wheat, Triticale, cereal rye seeds)	OC	Max seeds or pieces per 100 grams	25
Barley	BC	Max sees or pieces per 100 grams	20
Unmillable Material			
Soil (earth and sand) Pea sized or equivalent	EA	Max count per 100 grams	1
Stones Pea sized or equivalent	SE	Max count per 100 grams	1
Sticks Pea sized pieces or equivalent			NIL
INSECTS			
Live Stored Product Insects and Live Pea Weevil			NIL
TAINTS			
Any Tainting agent liable to impart an objectionable odour or taste			NIL
Musty and foreign odour			NIL
Foreign Flavour			NIL
Grain protectants or other agricultural chemicals not registered for the purpose or present in excess of legal residue limits			NIL
Staining and mould			NIL