

AusBulk Ltd
A.B.N 88 007 556 256
Broad Bean Receival Standards



2002/2003 Season Reference Chart.

Application

1. The following standards apply for the receival of BroadBeans
2. For details regarding the receival standards for all pulses refer to the AusBulk Commodity Classification Manual
3. Refer to the AusBulk Commodity Classification Manual Section 9 for all Weed Seed Limits not listed here.

| | | Grade description | Broad Beans |
|--|---|-------------------|---|
| | | Variety | Aquadulce, Toranto & Unknown |
| Screen Sizes | 14.0 mm Round Hole 11.0 mm Round Hole 6.0 mm Slotted | | |
| TEST CATEGORY | | TEST CODE | |
| Moisture | % max | MO | 13.0 |
| | | Instrument | Kett |
| | | Conversion | Faba Bean Conversion Scale |
| Purity | % min by weight | | 97 |
| Whole beans remaining above 14 mm screen | | 140 | No Limits |
| Whole beans remaining above 11 mm screen | | 110 | No Limits |
| Whole small beans remaining above 6 mm | | SB | No Limits |
| Screenings (Bean Material below 6 mm screen) | % max by weight | SC | 5 |
| Foreign material of which Unmillable material | % max by weight | TF | 3.0 |
| | | SA | 0.5 |
| TOTAL OFFAL consists of | | OF | 7 |
| >Defective Material of which Grub Eaten/insect Damage Mechanical Damage of which Any Kernel Damage Skin Damage | % max by weight | DG | 7 |
| | | | 1.5 |
| | | | 6 |
| | | | 3 |
| >Poor Colour Aschocyta Max 3% spots > 4 mm with no limit of spots <4 mm | | PC | 3 |
| | | | 3 |
| >Screenings | | SC | 5 |
| Snails Round or Conical | count in 500 grams | SNR/SNC | Max Two (2) snails or equivalent > 10mm And Max Five (5) whole or equivalent < 10mm |
| Field Insects | | | 15 maximum per 200 grams dead or alive |

AusBulk Ltd
A.B.N 88 007 556 256
Broad Bean Receival Standards
2002/2003 Season Reference Chart.



| WEED SEED CONTAMINANTS count per 500 grams | | CODE | COUNT |
|---|---|-----------------|--------------|
| Type 1: | Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy Horned), Wild Poppy. | S1 | 10 |
| Type 2: | Castor Oil Plant, Coriander, Crow Garlic/, Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort. | S2 | NIL |
| Type 3(a): | Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple. | 3A | 2 |
| Type 3(b): | Vetch (tare and commercial) | 3B | 5 |
| Type 3(c): | Heliotrope (blue and common) | 3C | 10 |
| Type 4: | Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent/Melilot (King Island), Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle. | S4 | 25 |
| Type 5: | Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Patternsons Curse, Sesbania Pea | S5 | 50 |
| Type 6: | Colombus Grass, Johnson, Grass, Saffron Thistle. | S6 | 12 |
| Type 7(a): | Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean. | 7A | 25 |
| Type 7(b): | Australian carrot, Barley, Barnyard grass, Bedstraw, Bindy-eye, Bifora, Bindweed, Brome grass, Burr grass, Buchan weed, Clover pods, Galvanised burr, Gromwell corn, Indian weed, Khaki weed, Linseed, Lucerne pod, Mallow, Medics pods, Millet Japanese, Muskweed, Oats common/black or wild, Onion weed, Paradoxa grass, Poached egg daisy, Rice, Rye cereal, Sheepweed, Sorghum grain, Spear thistle, Threehorn bedstraw, Tick grass, Triticale, Turnip weed ball, Wards weed, Wheat, Wheatgrass, Yellow Poverty weed. | 7B | 25 |
| Type 7(c): | Safflower, Sunflower | 7C | 2 |
| Type 8: | Bellvine | S8 | 250 |
| Small Foreign Seeds | Yellow Burrweed, Canola, Wild Turnip, Ryegrass, Lucerne Seed, Medic Seed, Clover Seed, Phalaris, Wireweed, Dock, Sow Thistle. | % max by weight | SS 2 |
| Objectionable Material | Free from animal excreta, rodents, live insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds/seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and/or contaminants imparting an odour, including caked, bin burnt or mouldy. | | NIL |