

**OAT RECEIVAL STANDARDS –
2002/2003 SEASON REFERENCE CHART**

PARAMETER		BINNED GRADE		
Test	Code	Grade code	Prime milling oat	Milling oat no. 1
			POAT	MOAT (MOA)
Variety	VR		EURO	Echidna, Euro, Swan, Dalyup, Mortlock, West, Murray, Pallinup
Moisture	MO	(max %)	12	12.5
Test weight	TW	min	52.5kg/hl	51.0kg/hl
Total impurities of which		Max % by weight	5.0	
Screenings Below the 2.0mm screen	SC	Max % by weight	5.0	10
Unmillable Above	SA	Max % by weight	2.0	
Total Foreign	TF	Max % by weight	2.0	
Other Oat Varieties	VA	Max % by weight	Nil	10
WEED SEED				
Small weed seeds	SW	Max % by volume	0.5	0.5
Melilotus Coriander or Garlic.			Nil	Nil
Large weed seeds	LW	Max by count from ½ litre	10	10
Three corner jacks	TJ	Max no per 1/2 litre	Nil	Nil
Heliotrope count above or below screen	53	Max no per 1/2 litre	4 seeds or 1 pod	4 seeds or 1 pod
Black or Wild Oats	BW	Max per ½ litre	5 per ½ litre	10 per ½ litre
Foreign grain	FG	Max % by 200 grains	1.0	1.0
DEFECTIVE GRAINS				
Shot Grain	SH	Max % by 200 grains	Nil	Nil
Sprouted Grain	SP		NIL	NIL
Green Oats	GO	Max % by 200 grains	1.0	5.0
Weather stained grains	WS	Max % by 200 grains	5.0	5.0
Weather stained kernels	WK	Max % by 200 grains	NIL	NIL
SNAILS Round	SNR	(max units per 1/2 litre)	2	2
Conical	SNC			
INSECTS		(max units per ½ litre)	Nil	Nil
Grain Live			Nil	Nil
Pea Weevil			Nil	Nil
Field – Live/Dead	FI	(max units ½ litre)	3	3
Dead Grain Insects	DI	(max units ½ litre)	5	5