

Ausbulk Ltd
A.B.N 88 007 556 256
Faba Bean Receival Standards
2002/2003 Season Reference Chart.



Application

1. The following standards apply for the receival of Faba Beans
2. For details regarding the receival standards for all pulses refer to the AusBulk Commodity Classification Manual
3. Refer Commodity Classification Manual Section 9 for Weed Seed Limits

Grade	FAB1	FIE1	FAB2	FIE2
Grade description	Australian No 1 Grade Faba Beans	Australian No 1 Grade Faba Beans.	Australian Faba Beans, Grade	Australian Fiesta Faba Beans
Variety	All Except Icarus	Fiesta & Manafest	All Except Icarus	Fiesta & Manafest

TEST CATEGORY

TEST CODE

Moisture	% max	MO	14.0			
	Instrument Conversion		Kett			
			Faba Bean			
Purity	% min by weight		97.0			
Defective material Including field mould (ascochyta blight)	% max by weight	DG	6.0% with max 3.0% BK	6.0% with max 3.0% BK	10.0% including PC	10.0% including PC
	% max by weight		max 3.0% PC	max 3.0% PC		
Poor colour	% max by weight	PC	3.0		7.0	
Screen Size	3.75mm slotted					
Foreign material Of which Unmillable material	% max by weight	TF	3.0			
		SA	0.5			
Snails	count from 200 grams	SN	2			
Ryegrass Ergot	2cm maximum, pieces laid end to end					
Field Insects	15 maximum per 200 grams dead or alive					

WEED SEED CONTAMINANTS count per 200 grams

CODE COUNT

Type 1:	Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy Horned), Wild Poppy.	S1	4
Type 2:	Castor Oil Plant, Coriander, Crow Garlic/, Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort.	S2	NIL
Type 3(a):	Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple.	3A	1
Type 3(b):	Vetch (tare and commercial)	3B	2
Type 3(c):	Heliotrope (blue and common)	3C	4
Type 4:	Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent/Melilot (King Island), Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle.	S4	10
Type 5:	Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea	S5	20
Type 6:	Colombus Grass, Johnson, Grass, Saffron Thistle.	S6	5
Type 7(a):	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean.	7A	10
Type 7(b):	Australian carrot, Barley, Barnyard grass, Bedstraw, Bindy-eye, Bifora, Bindweed, Brome grass, Burr grass, Buchan weed, Clover pods, Galvanised burr, Gromwell corn, Indian weed, Khaki weed, Linseed, Lucerne pod, Mallow, Medics pods, Millet Japanese, Muskweed, Oats common/black or wild, Onion weed, Paradoxa grass, Poached egg daisy, Rice, Rye cereal, Sheepweed, Sorghum grain, Spear thistle, Threehorn bedstraw, Tick grass, Triticale, Turnip weed ball, Wards weed, Wheat, Wheatgrass, Yellow Poverty weed.	7B	10
Type 7(c):	Safflower, Sunflower	7C	1
Small Foreign Seeds	Yellow Burrweed, Canola, Wild Turnip, Ryegrass, Lucerne Seed, Medic Seed, Clover Seed, Phalaris, Wireweed, Dock, Sow Thistle.	% max by weight	SS 1
Type 8:	Bellvine	S8	100
Objectionable Material	Free from animal excreta, rodents, live insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds/seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour, including caked, bin burnt or mouldy.		NIL