

**FEED OAT RECEIVAL STANDARDS –
2002/2003 SEASON REFERENCE CHART**

PARAMETER			BINNED GRADE		
Test	Code	Grade code	Feed no. 1	Feed no. 2	Feed no.3
			FOAT (FOA)	FOA2 (FO2)	FOA3
Variety	VR		All varieties except Saia, NZ Cape and Mortgage Lifter	All varieties except Saia, NZ Cape and Mortgage Lifter	All varieties except Saia, NZ Cape and Mortgage Lifter
Moisture	MO	(max %)	12.5	12.5	12.5
Test weight	TW	min	48.0kg/hl	47.5kg/hl	46kg/hl
Total impurities of which		Max % by weight			
Screenings Below the 2.0mm screen	SC	Max % by weight	20	40	40
Unmillable Above	SA	Max % by weight			
Total Foreign	TF	Max % by weight			
Other Oat Varieties	VA	Max % by weight	No limit	No limit	No Limit
WEED SEED					
Small weed seeds	SW	Max % by volume	3.0	5.0	5.0
Melilotus Coriander or Garlic.			Nil	Nil	NIL
Large weed seeds	LW	Max by count from ½ litre	40	65	65
Three corner jacks	TJ	Max no per 1/2 litre	5	5	5
Heliotrope count above or below screen	53	Max no per 1/2 litre	15	25	25
Black or Wild Oats	BW	Max per ½ litre	125	125	125
Foreign grain	FG	Max % by 200 grains	5.0	20.0	30
DEFECTIVE GRAINS					
Shot Grain	SH	Max % by 200 grains	No limit	No limit	No Limit
Sprouted Grain	SP		1.0	1.0	1
Green Oats	GO	Max % by 200 grains	No limit	No limit	No Limit
Weather stained grains	WS	Max % by 200 grains	20.0	30.0	50
Weather stained kernels	WK	Max % by 200 grains	20.0	20.0	20
SNAILS Round	SNR	(max units per 1/2 litre)	3	4	6
Conical	SNC				
INSECTS Grain Live		(max units per ½ litre)	Nil	Nil	NIL
Pea Weevil			Nil	Nil	NIL
Field – Live/Dead	FI	(max units ½ litre)	3	3	3
Dead Grain Insects	DI	(max units ½ litre)	5	5	5