



**WHEAT RECEIVAL STANDARDS 2002/03 SEASON SEED CONTAMINANT TYPES**

**AusBulk**

| <b>SEED CONTAMINANTS (S4-P9)</b>   |                     |    | ASW1 | AGP1 | FED1  |
|--|---------------------|----|------|------|---|
| <p>Tolerances for "Seed contaminants" apply to whole seeds or their equivalent in pieces per ½ litre.</p> <p>Tolerances stated in the table refer to the total of all seeds named in each type, <b>EXCEPT</b> for Type 1 which are tolerances for individual seeds. Any seed pods detected must be opened and the seeds counted for inclusion in the tolerance specified.</p>  |                     |    |      |      |   |
| <p><b>Type 1</b> - Individual (Per half litre)</p> <p>Colocynthis, 3 Corner Jack, Jute, Long Head Poppy, Mexican Poppy, Opium Poppy, Poppy (Field), Poppy (Horned), Wild Poppy, Parthenium Weed, New Zealand Spinach</p>   | Maximum Per Species | S1 | 8    | 8    | 8   |
| <p><b>Type 2</b> - Total (Per half litre)</p> <p>Broomrape, Castor Oil Plant, Coriander, Crow Garlic/Wild Garlic, Darling Pea, Ragweed, Rattlepods, Starburr, St. Johns Wort</p>   | Maximum             | S2 | NIL  | NIL  | NIL   |
| <p><b>Type 3a</b> - Total (Per half litre)</p> <p>Bathurst or Noogoora Burr, Bulls Head/Caltrop/Cats Head, Cape Tulip, Cottonseed, Dodder, Thornapple</p>  | Maximum             | 3A | 2    | 2    | 2   |
| <p><b>Type 3b</b> - Total (Per half litre)</p> <p>Vetch (Commercial &amp; Tare)</p>  | Maximum             | 3B | 4    | 4    | 4   |
| <p><b>Type 3c</b> - Total (Per half litre)</p> <p>Heliotrope (Blue or Common)</p>  | Maximum             | 3C | 8    | 8    | 8   |
| <p><b>Type 4</b> - Total (Per half litre)</p> <p>Bindweed (Field), Cutleaf Mignonette, Darnel (Drake Seed), Hexham Scent/Melilot (King Island)*, Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle,</p> <p>* Hexham Scent (Melilotus indicus) may only be received if there is no discernable tainting odour imparted to the wheat</p>  | Maximum             | S4 | 20   | 20   | 20  |
| <p><b>Type 5</b> - Total (Per half litre)</p> <p>Knapweed (Russian or Creeping), Sesbania Pea, Paterson's Curse/Salvation Jane</p>   | Maximum             | S5 | 40   | 40   | 40  |
| <p><b>Type 6</b> - Total (Per half litre)</p> <p>Columbus Grass, Johnson Grass, Saffron Thistle.</p>   | Maximum             | S6 | 10   | 50   | 50  |
| <p><b>Type 7</b> - Total (Per half litre)</p> <p>Chickpeas, Corn, Maize, Cowpea, Faba Beans, Lentils, Lupin, Field Peas, Safflower, Soybean, Sunflower.</p>  | Maximum             | S7 | 1    | 10   | 100   |
| <p><b>Type 8</b> - Total (Per half litre)</p> <p>Barley ( 2 row &amp; 6 row), Bindweed (Australian &amp; Black), Durum*, Red/Spring Feed W heats#, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum, (Grain) Triticale, Turnip Weed (Ball) + Any other seed contamination not specified in Types 1 – 8 or elsewhere in Small Foreign Seeds or Unmillable Material Above the screen.</p> <p>* Durum (Triticum durum) contamination of bread wheat</p> <p>#Tolerance in Australian FEED is unlimited</p> <p>#Red/Spring contamination in Australian FEED is unlimited</p> | Maximum             | S8 | 50   | 150  | 400*<br>No<br>Limit of<br>Durum<br>in<br>FEED |

**For the classification of any weed not listed above refer to the full listing in the Commodity Classification Manual 4.7.**