

SOFT WHEAT RECEIVAL STANDARDS – 2003/2004 SEASON REFERENCE CHART

Application

The following standard applies to the receipt of Soft wheat

Standard

1. The wheat must be of the varieties Anlace (A7), Bindawarra (B1), Bowie (B3), Buckley (B10), Corrigan (C10), Datatine (D7), Tatiara (T9), Tincurrin (T1), Vectis (V3, Wyuna (W7).
 2. SFE1 grades must conform to the AWB general Wheat Receival Standards for the ASW1 grade.
- ❖ Subject to DBS on a site by site basis

Category		Test Code	SFE1	SFE2
Test Weight	Minimum	TW	74	68
Protein content	Maximum %	PR	9.5%	11.5%
Screenings below the screen	Maximum (% by weight)	SC	5❖ <small>Subject to DBS</small>	10%
Unmillable material above the screen	Maximum (% by weight)	SA	0.6%	1.2%
Small Foreign Seeds	Maximum (% by weight)	SS	0.6%	1.2%

DEFECTIVE GRAINS

Sprouted Grains

WHERE NO FALLING NUMBER EQUIPMENT IS AVAILABLE ON SITE

	Maximum % by count	SP	1	2
Minimum site daily running sample			300	200
		WHERE FALLING NUMBER EQUIPMENT IS AVAILABLE ON SITE.		
Falling Number	Minimum (seconds)	FN	300	200
Stained Grains	Maximum % by count	FS	5	15
Of Which				
Pink Grains	Maximum % by count	PF	2	5
Dry Green/Sappy/Frost Distorted	Maximum % by count	GS	1	10
Type 6	Maximum seeds per ½ litre	S6	10	50
Type 7	Maximum seeds per ½ litre	S7	1	10
Type 8 (Foreign Grain)	Maximum seeds per ½ litre	S8	50	150

NOTES:

- 1 Any loads that do not comply with these minimum standards for Soft are to be classified as AGP1 wheat. (Note: loads must also conform to the general wheat receival standards for AGP1 or FED1 to be classified as AGP1 or FED1).
- 2 Where a load is classified at a grade lower than SOFT, record on the Transaction Note the additional test with the appropriate Test Code and Value. For Test Codes not listed refer to the 2003/2004 AusBulk Wheat Receival Chart.
- 3 The maximum varietal classification for loads that fail the Soft grade is AGP1.