

# Feed Oat Receival Standards FOAT / FOAT2 Season 2005/2006

| PARAMETER   |      | BINNED GRADE            |  |  |
|---|------|-------------------------|--|--|
| Test  | Code | Grade code              | Feed No. 1   | Feed No. 2   |
|   |      |                         | FOAT (FOA)   | FOA2 (FO2)   |
| Variety   | VR   |                         | All varieties except Saia, NZ Cape and Mortgage Lifter | All varieties except Saia, NZ Cape and Mortgage Lifter |
| Moisture  | MO   | (Max %)                 | 12.5   | 12.5   |
| Test weight   | TW   | Kg/hl min               | 48.0   | 47.5   |
| <b>Total impurities<br/>Of Which</b>  |      | Max % by weight         | NA   | NA   |
| Screenings - below the 2.0mm slotted screen   | SC   | Max % by weight         | 20   | 40   |
| Unmillable Above  | SA   | Max % by weight         | NA   | NA   |
| Total Foreign   | TF   | Max % by weight         | NA   | NA   |
| Other Oat Varieties   | VA   | Max % by weight         | No Limit   | No Limit   |
| <b>Defective Grains</b>   |      |                         |  |  |
| Damaged Grains  | DS   | Max % by 200 grains     | No Limit   | No Limit   |
| Weather stained grains  | WS   | Max % by 200 grains     | 20   | 30   |
| Weather stained kernels   | WK   | Max % by 200 grains     | 20   | 20   |
| Field Fungi   |      | Max % by 200 grains     | NIL  | NIL  |
| Dry Green/Sappy Green   | GO   | Max % by 200 grains     | No Limit   | No Limit   |
| Frost Damaged   | FR   | Max % by 200 grains     | 20   | 20   |
| Insect Damage   | ID   | Max % by 200 grains     | 5  | 5  |
| Sprouted Grain  | SP   | Max % by 200 grains     | No Limit   | No Limit   |
| • Early   | SH   |                         | NIL  | NIL  |
| • Advanced  |      |                         |  |  |
| <b>Seed Contaminants – * Individual seed basis – Note: Refer section 7 CCM for seed contaminant list</b>  |      |                         |  |  |
| Type 1*   | S1*  | Max / ½litre in total   | 5  | 5  |
| Type 2  | S2   | Max / ½litre in total   | NIL  | NIL  |
| Type 3a   | 3A   | Max / ½litre in total   | NIL  | NIL  |
| Type 3b   | 3B   | Max / ½litre in total   | 4  | 4  |
| Type 3c   | 3C   | Max / ½litre in total   | 4  | 4  |
| Type 4  | S4   | Max / ½litre in total   | 10   | 10   |
| Type 5  | S5   | Max / ½litre in total   | 40   | 40   |
| Type 6  | S6   | Max / ½litre in total   | 10   | 10   |
| Type 7  | S7   | Max / ½litre in total   | 20   | 40   |
| Type 8  | S8   | Max / ½litre in total   | 250  | 500  |
| Small Foreign Seeds   | SS   | Max% by weight          | Max 100 Black / Wild Oats<br>3                         | Max 125 Black / Wild Oats<br>5                         |
| <b>Other Contaminants</b>   |      |                         |  |  |
| <b>NIL</b> Tolerance for Objectionable Matter, Heat Damaged, Bin Burnt, Pickled or Coloured grain, Odours, Sour Musty or Post Harvest Mouldy Grain and Chemical Residues. |      |                         |  |  |
| Smuts / Cereal Ergot  |      | Max count per 1/2 litre | NIL  | NIL  |
| Ryegrass Ergot  | RE   | Max length              | 2 cm   | 2cm  |
| Snails Round  | SNR  | Max count per 1/2 litre | 3  | 4  |
| Conical   | SNC  |                         |  |  |
| Stored Grain Insects<br>(Includes Peas Weevil)  |      | Max count per 1/2 litre |  |  |
| • Alive   | LI   |                         | Nil  | Nil  |
| • Dead  | DI   |                         | 5  | 5  |
| Field – Live/Dead   | FI   | Max count per 1/2 litre | 3  | 3  |
| Sitonia Weevil  | SI   | Max count per 1/2 litre | 10   | 10   |
| Sand - Grains   | ES   | Max count per 1/2 litre | 50   | 50   |
| Earth – Pea size pieces   | EA   | Max count per 1/2 litre | 3  | 3  |