

Feed Oat Receival Standards FOAT / FOA2 Season 2006/2007

PARAMETER		BINNED GRADE		
Test	Code	Grade code	Feed No. 1	Feed No. 2
			FOAT (FOA)	FOA2 (FO2)
Variety	VR		All varieties except Saia, NZ Cape and Mortgage Lifter	All varieties except Saia, NZ Cape and Mortgage Lifter
Moisture	MO	(Max %)	12.5	12.5
Test weight	TW	Kg/hl min	48.0	47.5
Total impurities Of Which		Max % by weight	NA	NA
Screenings - below the 2.0mm slotted screen	SC	Max % by weight	20	40
Unmillable Above	SA	Max % by weight	NA	NA
Total Foreign	TF	Max % by weight	NA	NA
Other Oat Varieties	VA	Max % by weight	No Limit	No Limit
Defective Grains				
Damaged Grains	DS	Max % by 200 grains	No Limit	No Limit
Weather stained grains	WS	Max % by 200 grains	20	30
Weather stained kernels	WK	Max % by 200 grains	20	20
Field Fungi		Max % by 200 grains	NIL	NIL
Dry Green/Sappy Green	GO	Max % by 200 grains	No Limit	No Limit
Frost Damaged	FR	Max % by 200 grains	20	20
Insect Damage	ID	Max % by 200 grains	5	5
Sprouted Grain	SP	Max % by 200 grains	No Limit	No Limit
• Early	SH		NIL	NIL
• Advanced				
Seed Contaminants – * Individual seed basis – Note: Refer section 7 CCM for seed contaminant list				
Type 1*	S1*	Max / ½litre in total	5	5
Type 2	S2	Max / ½litre in total	NIL	NIL
Type 3a	3A	Max / ½litre in total	NIL	NIL
Type 3b	3B	Max / ½litre in total	4	4
Type 3c	3C	Max / ½litre in total	4	4
Type 4	S4	Max / ½litre in total	10	10
Type 5	S5	Max / ½litre in total	40	40
Type 6	S6	Max / ½litre in total	10	10
Type 7	S7	Max / ½litre in total	20	40
Type 8	S8	Max / ½litre in total	250	500
Small Foreign Seeds	SS	Max% by weight	Max 100 Black / Wild Oats 3	Max 125 Black / Wild Oats 5
Other Contaminants				
NIL Tolerance for Objectionable Matter, Heat Damaged, Bin Burnt, Pickled or Coloured grain, Odours, Sour Musty or Post Harvest Mouldy Grain and Chemical Residues.				
Smuts / Cereal Ergot		Max count per 1/2 litre	NIL	NIL
Ryegrass Ergot	RE	Max length	2 cm	2cm
Snails Round	SNR	Max count per 1/2 litre	3	4
Conical	SNC			
Stored Grain Insects (Includes Peas Weevil)		Max count per 1/2 litre		
• Alive	LI		Nil	Nil
• Dead	DI		5	5
Field – Live/Dead	FI	Max count per 1/2 litre	3	3
Sitonia Weevil	SI	Max count per 1/2 litre	10	10
Sand - Grains	ES	Max count per 1/2 litre	50	50
Earth – Pea size pieces	EA	Max count per 1/2 litre	3	3