

Soft Wheat Receival Standards SA Season 2007/2008

Standard

- The wheat must be of the varieties Anlace (A7), Bindawarra (B1), Bowie (B3), Buckley (B10), Corrigan (C10), Datatine (D7), Tatiara (T9), Tincurrin (T1), Vectis (V3), Wyuna (W7).
 - Check the Wheat Variety Codes SA summary chart for this season to determine maximum bin grades for SOFT varieties.
- ❖ Subject to DBS

Category		Test Code	SFE1	SFE2
Test Weight	Minimum	TW	74	68
Protein content	Maximum %	PR	9.5%	10.5%
Moisture Content	Maximum %	MO	13.5	
Screenings below the screen	Maximum (% by weight)	SC	5❖ Subject to DBS	10%
Unmillable material above the screen	Maximum (% by weight)	SA	0.6%	1.2%
Small Foreign Seeds	Maximum (% by weight)	SS	0.6%	1.2%
DEFECTIVE GRAINS				
Sprouted Grains		Where no falling numbers equipment is available on site		
(300 grain sample)	Maximum % by count	SP	NIL	
Minimum site daily running sample			300	200
Where falling number equipment is available on site				
Falling Number	Minimum (seconds)	FN	300	200
Stained Grains Of Which Pink Grains	Maximum % by count	FS	5	15
	Maximum % by count	PF	2	5
Dry Green/Sappy/Frost Distorted	Maximum % by count	GS	1	10
CONTAMINANTS				
Type 6	Maximum seeds per ½ litre	S6	10	50
Type 7	Maximum seeds per ½ litre	S7	1	10
Type 8 (Foreign Grain)	Maximum seeds per ½ litre	S8	50	150

NOTES:

- As per ASW1 tolerances.
- Loads not received into the SFE1 and SFE2 grades must conform to the receival standards for any other grade the load is received as – AGP1 or FED1.
- Where a load is classified at a grade lower than SOFT, record on the Transaction Note the additional test with the appropriate Test Code and Value. For Test Codes not listed refer to the 2007/2008 ABB Grain Ltd Wheat Receival Standards.