

Field Pea Receival Standards Season 2007/2008

The following standards apply for the receival of Field Peas

- For details regarding the receival standards for all pulses refer to the ABB Commodity Classification Manual
- The Field Peas shall be hard & well filled

| Screen Size 3.75 mm Slotted | Grade | | PEAS | PEAK | PEAW |
|--------------------------------|--|-----------|---|------------|------------|
| | Grade description | | Field Peas | Kaspa Peas | White Peas |
| Test Category | | Test Code | | | |
| Moisture | % Max | MO | 14.0 | | |
| | Instrument Conversion | | Kett Pea | | |
| Purity | % Min by weight | | 97.0 | | |
| Defective Material | % Max by weight | DG | 7.0 | | |
| Foreign Material | % Max by weight | TF | 3.0 | | |
| Of Which Unmillable Matter | | SA | 0.5 | | |
| Of Which Soil | | EA | 0.3 | | |
| Stones | Count | SE | Stones are part of soil. Record the number - it does not matter how many but ensure they do not exceed the 0.3% tolerance for soil. | | |
| Snails – Round or Conical | Count from 200 grams | SNR/SNC | 1 dead or alive | | |
| Field Insects | 15 maximum per 200 grams dead or alive | | | | |
| Ryegrass Ergot | 2cm maximum, pieces laid end to end | | | | |

Weed Seed Contaminants Count per 200 Grams *Type 1 Individual Seed Basis

| | | Code | Count |
|-------------------------------|---|-----------------|---------------|
| Type 1 | Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy (Horned), Wild Poppy | S1* | 4 |
| Type 2 | Castor Oil Plant, Coriander, Crow Garlic / Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort | S2 | NIL |
| Type 3(a) | Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple | 3A | 1 |
| Type 3(b) | Vetch (tare and commercial) | 3B | 2 |
| Type 3(c) | Heliotrope (blue and common) | 3C | 4 |
| Type 4 | Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent (Melilotus) [†] , Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle | S4 | 10 |
| Type 5 | Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea | S5 | 20 |
| Type 6 | Colombus Grass, Johnson, Grass, Saffron Thistle, Clover (Pods), Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Wild Radish (Pods), Trefoil (Pods) (Pods refer to whole pods or part thereof) | S6 | 5 |
| Type 7(a) | Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean | 7A | 10 |
| Type 7(b) | Barley(2 row), Barley (6 row), Bindweed (Australian), Bindweed (Black), Durum, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum (Grain), Triticale, Turnip Weed, Wheat | 7B | 10 |
| Type 7(c) | Safflower, Sunflower | 7C | 1 |
| Type 8 | Bellvine | S8 | 100 |
| Small Foreign Seeds | See CCM section 9 for complete list | % Max by weight | SS 0.6 |
| Objectionable Material | Free from animal excreta, rodents (live or dead), live stored product insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds / seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour not normally associated with that pulse and toxic and / or noxious weed seeds prohibited by state laws against inclusion in stockfeed. | | NIL |

[†] Hexham scent may only be received if there is no discernible tainting odour imparted on the grain