

Field Pea Receival Standards Season 2009/2010

The Field Peas shall be hard & well filled

- Sample Size = 200 grams

Screen Size	Grade	PEAS	PEAK	PEAW
3.75 mm Slotted	Grade description	Field Peas	Kaspa Peas	White Peas
Test Category		Test Code		
Moisture	% Max	MO	14.0	
	Instrument Conversion		Kett	
			Pea	
Purity	% Min by weight		97.0	
Defective Material	% Max by weight	DG	7.0	
Mould (Field or Storage) % by weight			NIL	
Foreign Material		TF	3.0	
Of Which	% Max by weight	SA	0.5	
Unmillable Matter		EA	0.3	
Of Which				
Soil				
Stones	Max Count / 200 grams	SE	Stones are part of SA. Record the number - it does not matter how many but ensure they do not exceed the 0.5% tolerance.	
Snails – Round or Conical	Max Count / 200 grams	SNR/SNC	1 Dead or Alive	
Field Insects	Max Count / 200 grams	FI	15 Dead or Alive	
Ryegrass Ergot – Length in cm	Max no. of pieces laid end to end	RE	2 cm	

Foreign Seed Contaminants Max Count per 200 Grams *Type 1 Individual Seed Basis

		Code	Count
Type 1*	Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy (Horned), Wild Poppy	S1*	4
Type 2	Castor Oil Plant, Coriander, Crow Garlic / Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort	S2	NIL
Type 3(a)	Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple	3A	1
Type 3(b)	Vetch (tare and commercial)	3B	2
Type 3(c)	Heliotrope (blue and common)	3C	4
Type 4	Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent (Melilotus) ¹ , Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle ¹ Hexham scent may only be received if there is no discernible tainting odour imparted on the grain	S4	10
Type 5	Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea	S5	20
Type 6	Colombus Grass, Johnson Grass, Saffron Thistle, Clover (Pods), Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Wild Radish (Pods), Trefoil (Pods) (Pods refer to whole pods or part thereof)	S6	5
Type 7(a)	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean	7A	10
Type 7(b)	Barley(2 row), Barley (6 row), Bindweed (Australian), Bindweed (Black), Durum, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum (Grain), Triticale, Turnip Weed, Wheat	7B	10
Type 7(c)	Safflower, Sunflower	7C	1
Type 8	Bellvine	S8	100
Small Foreign Seeds	See CCM section 9 for complete list	% Max by weight	SS 0.6
Objectionable Material	<ul style="list-style-type: none"> • Free from animal excreta, rodents (live or dead), live stored product insect pests, any chemical not registered for use on pulses or in excess of legal tolerances, pickling compounds / seed dressings or any fungicide added to the pulse as a seed dressing. • Any tainting agents and / or contaminants imparting an odour not normally associated with that pulse, any commercially objectionable odour / or an odour not normally associated with the pulse. • Any toxic and / or noxious weed seeds prohibited by state laws against inclusion in stockfeed. • Any other commercially unacceptable contaminant such as glass, metal, fertiliser, concrete. 		NIL