

## Wheat Seed Contaminant Types Receival Standard Chart 2005/2006

<b>SEED CONTAMINANTS (For a detailed listing refer to the CCM section 4)</b>			ASW1	AGP1	FED1
Tolerances for "Seed contaminants" apply to whole seeds or their equivalent in pieces per ½ litre. Tolerances stated in the table refer to the total of all seeds named in each type, <b>EXCEPT</b> for Type 1 which are tolerances for individual seeds. Any seed pods detected must be opened and the seeds counted for inclusion in the tolerance specified.					
<b>Type 1 - Individual (Per half litre)</b> Colocynth, 3 Corner Jack / Double Gees / Spiny Emex, Jute, Long Head Poppy, Mexican Poppy, Opium Poppy, Poppy (Field), Poppy (Horned), Wild Poppy, Parthenium Weed, New Zealand Spinach	Maximum Per Species	S1	8	8	8
<b>Type 2 - Total (Per half litre)</b> Branched Broomrape, Castor Oil Plant, Coriander, Crow Garlic/Wild Garlic, Darling Pea, Ragweed, Rattlepods, Starburr, St. Johns Wort	Maximum	S2	NIL	NIL	NIL
<b>Type 3a - Total (Per half litre)</b> Bathurst or Noogoora Burr, Bulls Head/Caltrop/Cats Head, Cape Tulip, Cottonseed, Dodder, Thornapple	Maximum	3A	2	2	2
<b>Type 3b - Total (Per half litre)</b> Vetch (Commercial & Tare)	Maximum	3B	4	4	4
<b>Type 3c - Total (Per half litre)</b> Heliotrope (Blue or Common)	Maximum	3C	8	8	8
<b>Type 4 - Total (Per half litre)</b> Bindweed (Field), Cutleaf Mignonette, Darnel (Drake Seed), Hexham Scent/Melilot (King Island)*, Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle, * Hexham Scent (Melilotus indicus) may only be received if there is no discernable tainting odour imparted to the wheat	Maximum	S4	20	20	20
<b>Type 5 - Total (Per half litre)</b> Knapweed (Russian or Creeping), Sesbania Pea, Paterson's Curse/Salvation Jane	Maximum	S5	40	40	40
<b>Type 6 - Total (Per half litre)</b> Columbus Grass, Johnson Grass, Saffron Thistle.	Maximum	S6	10	50	50
<b>Type 7 - Total (Per half litre)</b> Chickpeas, Corn, Maize, Cowpea, Faba Beans, Lentils, Lupin, Field Peas, Safflower, Soybean, Sunflower.	Maximum	S7	1	10	100
<b>Type 8 - Total (Per half litre)</b> Barley ( 2 row & 6 row), Bindweed (Australian & Black), Durum*, Red/Spring Feed Wheats#, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum, (Grain) Triticale, Turnip Weed (Ball) + Any other seed contamination not specified in Types 1 – 8 or elsewhere in Small Foreign Seeds or Unmillable Material Above the screen. * Durum (Triticum durum) contamination of bread wheat #Tolerance in Australian FEED is unlimited #Red/Spring contamination in Australian FEED is unlimited	Maximum	S8	50	150	400* No Limit of Durum in FEED