

BARLEY RECEIVAL STANDARDS VIC 2002/2003

These Standards are to be applied on individual truck loads and must not be averaged over a number of loads

	Code	Varietal Grade	Malting Barley		Feed Barley	
			MALT1	MALT 3	FEED 1	FEED 2
		Franklin	FR1		F1	F2
		Gairdner	GA1			
		Schooner	SC1	SC3		
		Sloop	SL1	SL3		
		Sloop SA				
		Sloop VIC				
Varietal Purity min (%)			95		All 2 Row Varieties	
Test Weight min (kg/hl)	TW		65.0		62.5	60.0
Moisture max (%) – Regional variations apply	MO		12.5		12.5	
Protein Content (%) – Minimum	PR		9.0		NA	
Maximum			12.0	12.8	NA	
Screenings (% by weight) Below 2.5mm screen (all varieties except Franklin)	SC		30.0	42.0	60.0	80.0
Below 2.2mm screen (all varieties except Franklin)	SC22		7.0	NA	NA	
Franklin Malting Barley only Below 2.2mm screen	SC22		10.0	NA	NA	
Germinative Energy min (%) (Late deliveries only, after 1 st March)	GE		95		NA	
Germinative Capacity min (%) (Late deliveries only, after 1 st March)	GC		98		NA	
RVA	RV		130		NA	
Defective Barley Grains- Maximum tolerance by Count						
Shot and Sprouted Grains (count per 100 grains)	SH		NIL		Free from root system	5 sprouted
Split germ and/or a more advanced stage in which germ is grown	SP					
Field Fungi and Dark Tipped Grains (count per 100 grains)	DC		10		NA	
Skinnings (count per 100 grains)	SK		15		NA	
Bored Insect Damaged Barley (count per half litre)	ID		10		85	
Split/Cleaved Barley - Internal Split (count per 100 grains)	CB		1		NA	
Cracked / Broken Grains (% weight per 100 grams)	CK		2		5	
Frost Damaged (count per 100 grains)	FR		5		10	
Dry Green Sappy Barley (count per 100 grains)	GB		1		NA	
Grain Contaminants – Tolerances apply to whole seeds or their equivalent in pieces and refer to the maximum total of all seeds named in each type per half litre						
Wheat/Cereal Rye/Triticale/Rice/Cultivated Oats	FG		85		500	1500
Wild Oats/Wild Radish	BW		25		50	100
Barley with Blue Aleurone Layer	VA		NIL		100	
Other Seed Contaminants- Tolerances apply to whole seeds or their equivalent in pieces and refer to the maximum total of all seeds named in each type per half litre, *Except type 1 in which the maximum applies on an individual seed basis per half litre						
Type 1 : Colocynth, Field Poppy, Horned Poppy, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Saffron Thistle, Wild Poppy	(S1)*		8		8	
Type 2 : Castor Oil Plant, Coriander, Crow Garlic or Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St Johns Wort, Broomrape.	(S2)		NIL		NIL	
Type 3a : Bathurst Burr, Bulls Head/Caltrop/Cats Heads, Cape Tulip, Cotton Seed, Dodder, Noogoora Burr, Thornapple, Bellvine.	(3a)		2		2	
Type 3b : Vetch Tare, Vetch (Commercial).	(3b)		4		4	10
Type 3c : Blue Heliotrope, Common Heliotrope.	(3c)		1 pod/4 seeds			
Type 3d : Double Gee/Spiny Emex/Three Corner Jack.	(3d)		1			
Type 4 : Cutleaf Mignonette, Darnel (Drake Seed), Field Bindweed, Hexham Scent**, Hoary Cress, Mintweed, Melilot (King Island), Night Shades, Paddy Melon, Skeleton Weed, Variegated Thistle, Parthenium Weed***.	(S4)		20			
Type 5 : Creeping Knapweed/Russian Knapweed, Pattersons Curse/Salvation Jane, Sesbania Pea.	(S5)		40			
Type 6 : Columbus Grass, Johnson Grass	(S6)		NIL		40	
Type 7 : Sunflower and any other large (pea sized) seeds or pods	(S7)		1		10	20
Type 8 : Australian Bindweed, Bedstraw, Black Bindweed, Brome Grass, Forage Sorghum, Muskweed, Onion Weed, Phalaris Glumes, Poverty Weed, Sheep Weed, Turnip Weed and any other weeds not specified in types 1-7 or SS	(S8)		50		150	300
Small Foreign Seeds not specified in types 1-8 below specified sieve (by weight)	SS		0.6%		1.2%	2.0%
* Individual Seed Basis ** Hexham Scent is only acceptable if no tainting odour is present *** Parthenium has a NIL tolerance in NSW/VIC/SA						
Other Contaminants – Tolerances apply to whole seeds or their equivalent in pieces and refer to the maximum total of all contaminants named in each type per half Litre *Except for stones in which the maximum applies on a one litre sample						
Cereal Smuts/Cereal Ergots			NIL			
Ergot of Ryegrass (tolerance applies to the max. length when pieces are aligned)	RE		0.5cm			
Soil (Pea size pieces by count)	EA		3			
Sand (Grains by count)	ES		50			
Stones (units per litre)	SE		NIL			
Field Insects (Field Insects by count)	FI		3			
Sitona Weevils (Sitona weevils by count)	SI		10			
Grain Insects : Live (Live insect pests of stored grain by count)			NIL			
: Dead (Dead insect pests of stored grain by count)	DI		10			
Snails (Max. no. per half litre by count)			2		2	4
Snails – Round	SNR					
Snails – Conical	SNC					
Odours, Sour and Musty or Mouldy grains (Grain which has any commercially objectionable foreign odour due to tainting agents or improper storage causing mould, souring or musty odours)			NIL			
Objectionable Matter (Sticks, glass, concrete, or any other commercially unacceptable contaminant, smell or taste. Fusarium (pink) fungal stained and/or post-harvest mouldy grain) Pickled grain			NIL			
Foreign Material (Other than already specified – max % by weight)	TF		1			
Chemical Residues (Residues of any chemical compound not approved for barley, or use in contravention of the labeled instructions)			NIL			