

Australian Bulk Alliance
A.B.N 39 087 280 260
CANOLA RECEIVAL STANDARDS
2003/2004 SEASON REFERENCE CHART



Grade	Moisture	Test weight	Foreign material By weight	Wild turnip By count	Broken seeds By count	Total defective	OF	Damaged seeds (bin burnt, frosted, weather damaged) By weight	Sprouted seeds By count	Green seeds By count
TEST CODE	MO	TW	TF	WT	BK	DG*	WHICH	DS	SP	GN
CANO	Max 8.0%	Min 62	Max 3.0%	Max 3.0%	Max 7.0%	Max 10.0%		Max 3.0%	Max 5.0%	Max 2.0%
CAN 2	Max 8.0%	Min 62	Max 3.0%	Max 3.0%	Max 7.0%	Max 20.0%		Max 5.0%	Max 5.0%	Max 10.0%

*Total Defective is the addition of Damaged Seeds, Sprouted Seeds, Green Seeds

There is a limit of no more than 1 snails/stones or equivalent in a ½ litre passing through a 3.0mm round hole screen.

There is a NIL tolerance for any stones remaining above a 3.0mm round hole screen (2.25 litre sample size).

There is a tolerance of 1 snail or equivalent remaining above a 3.0mm round hole screen (5.0 litre sample size).

Restricted Seed Contaminants

(Limit per 1/2 litre Sample)

Burrs (Xanthium Spp)	1	Jute	3
Common Heliotrope	3	Thornapple	2
Crow Garlic	2	Nightshade	3
Sesbania Pea	60	Wild Mignonette	1
Skeleton Weed	2		
Hexham Scent	3		
Mexican Poppy	3		
Darnel	3		
Mint Weed	3		

Nil Tolerance Seed Contaminants

Any other Tainting Agents, or contaminant imparting an objectionable odour.

Alligator Weed	<i>Alteranthera philoxeroides</i>	Rattlepod	<i>Crotalaria spp</i>
Cape Tulip	<i>Homeria spp</i>	Saffron Thistle	<i>Carthamus lanatus</i>
Castor Oil Plant	<i>Ricinus communis L</i>	Dodder	<i>Cuscuta spp</i>
Creeping Knapweed	<i>Acoptilon repens</i>	Giant Sensitive Plant	<i>Mimosa invisia</i>
Darling Pea	<i>Swansonia spp</i>	Star Burr	<i>Acanthospermum hispidum</i>
Parthenium Weed	<i>Parthenium hysterophorus</i>	Stinkwort	<i>Inula graveolens</i>
Ragweed	<i>Ambrosia spp</i>	St Johns Wort	<i>Hypericum perforatum L</i>
Opium Poppy	<i>Papaver somniferum L</i>	Calomba daisy	<i>Pentzia suffrutcosa</i>
Coriander	<i>Coriandrum sativum</i>		