

Soft Wheat Receival Standards Season 2005/2006

Standard

- The wheat must be of the varieties Anlace (A7), Bindawarra (B1), Bowie (B3), Buckley (B10), Corrigan (C10), Datatine (D7), Tatiara (T9), Tincurrin (T1), Vectis (V3), Wyuna (W7).
- Check the Wheat Variety Codes SA summary chart for this season to determine maximum bin grades for SOFT varieties.

❖ Subject to DBS

Category		Test Code	SFE1	SFE2
Test Weight	Minimum	TW	74	68
Protein content	Maximum %	PR	9.5%	11.5%
Moisture Content	Maximum %	MO	13.5	
Screenings below the screen	Maximum (% by weight)	SC	5❖ Subject to DBS	10%
Unmillable material above the screen	Maximum (% by weight)	SA	0.6%	1.2%
Small Foreign Seeds	Maximum (% by weight)	SS	0.6%	1.2%
DEFECTIVE GRAINS				
Sprouted Grains		Where no falling numbers equipment is available on site		
(300 grain sample)	Maximum % by count	SP	NIL	
Minimum site daily running sample			300	200
Where falling number equipment is available on site				
Falling Number	Minimum (seconds)	FN	300	200
Stained Grains	Maximum % by count	FS	5	15
Of Which	Maximum % by count	PF	2	5
Pink Grains	Maximum % by count	GS	1	10
Dry Green/Sappy/Frost Distorted	Maximum % by count	GS	1	10
CONTAMINANTS				
Type 6	Maximum seeds per ½ litre	S6	10	50
Type 7	Maximum seeds per ½ litre	S7	1	10
Type 8 (Foreign Grain)	Maximum seeds per ½ litre	S8	50	150

NOTES:

- Loads not received into the SFE1 and SFE2 grades must conform to the receival standards for any other grade the load is received as – ASW1, AGP1 or FED1.
- Where a load is classified at a grade lower than SOFT, record on the Transaction Note the additional test with the appropriate Test Code and Value. For Test Codes not listed refer to the 2005/2006 ABB Grain Ltd Wheat Receival Standards.