

Faba Beans Receival Standards Season 2006/2007

1. The following standards apply for the receival of Faba Beans
2. For details regarding the receival standards for all pulses refer to the ABA Commodity Classification Manual
3. Faba Beans shall be, sound, dry, fresh and light to medium brown or pale green in colour.

Grade	FAB1	FIE1	FAB2	FIE2
Grade description	Australian No 1 Grade Faba Beans	Australian No 1 Grade Faba Beans	Australian Faba Beans Grade	Australian Fiesta Faba Beans
Variety	All Except Icarus	Fiesta Manafest Farah	All Except Icarus	Fiesta Manafest Farah

TEST CATEGORY

TEST CODE

Moisture	% Max	MO	14.0			
	Instrument Conversion		Kett			
			Faba Bean			
Purity	% Min by weight		97.0			
Defective material Including field & storage mould	% Max by weight	DG	6.0% with max 3.0% BK	6.0% with max 3.0% BK	10.0% including PC	10.0% including PC
	% Max by weight		max 3.0% PC	max 3.0% PC		
Poor colour (ascochyta)	% Max by weight	PC	3.0		7.0	
Screen Size	3.75mm slotted					
Foreign material Of which Unmillable material Of Which Soil	% Max by weight	TF	3.0			
		SA	0.5			
		EA	0.3			
Stones	Count	SE	Stones are part of soil. Record the number - it does not matter how many but ensure they do not exceed the 0.3% tolerance for soil.			
Snails – Dead or Alive	Count from 200 grams	SN	1			
Ryegrass Ergot	2cm maximum, pieces laid end to end					
Field Insects	15 maximum per 200 grams dead or alive					

WEED SEED CONTAMINANTS count per 200 grams - *Type 1 individual seed basis **CODE COUNT**

Type 1:	Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy (Horned), Wild Poppy.	S1*	4
Type 2:	Castor Oil Plant, Coriander, Crow Garlic / Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort.	S2	NIL
Type 3(a):	Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple.	3A	1
Type 3(b):	Vetch (tare and commercial)	3B	2
Type 3(c):	Heliotrope (blue and common)	3C	4
Type 4:	Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent/Melilot (King Island) No discernible tainting Odour , Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle.	S4	10
Type 5:	Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea	S5	20
Type 6:	Colombus Grass, Johnson, Grass, Saffron Thistle, Clover (Pods), Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Wild Radish (Pods), Trefoil (Pods),. (Pods refer to whole pods or part thereof)	S6	5
Type 7(a):	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean.	7A	10
Type 7(b):	Barley(2 row), Barley (6 row), Bindweed (Australian), Bindweed (Black), Durum, Lucerne (pods), Medic (pods), Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum (Grain), Trefoil (Pods), Triticale, Turnip Weed, Wheat.	7B	10
Type 7(c):	Safflower, Sunflower	7C	1
Type 8:	Bellvine	S8	100
Small Foreign Seeds	Yellow Burrweed, Canola, Wild Turnip, Ryegrass, Lucerne Seed, Medic Seed, Clover Seed, Phalaris, Wireweed, Dock, Sow Thistle.	% max by weight	SS 0.6
Objectionable Material	Free from animal excreta, rodents, live insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds/ seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour not normally associated with that pulse.		NIL