

	<b>1657</b> VERSION 1	<b>RECEIVAL STANDARDS FOR FABA BEANS</b>				<b>2007/2008 SEASON</b>
	DOCUMENT DATE	1/10/07	OWNER	APPLICATION	All ABA	

- The following standards apply for the receipt of Faba Beans
- For details of definitions used for all pulses refer to the ABB Commodity Classification Manual, including Weed Seed Limits
- Faba Beans shall be, sound, dry, fresh and light to medium brown or pale green in colour
- Sample size 400 grams

Screen Size	Grade	FAB1	FIE1	FAB2	FIE2	
3.75mm slotted	Grade description	Australian No 1 Grade Faba Beans	Australian No 1 Grade Faba Beans	Australian Faba Beans Grade	Australian Fiesta Faba Beans	
	Variety	All Except Icarus	Fiesta Manifest Farah, Nura	All Except Icarus	Fiesta Manifest Farah, Nura	
<b>Test Category</b>		<b>Test Code</b>				
<b>Moisture</b>	% Max	MO	14.0			
	<b>Instrument Conversion</b>		<b>Kett Faba Bean</b>			
<b>Purity</b>	% Min by weight		97.0			
<b>Total Defective Seeds</b> Of Which <b>Defective</b> Includes broken, damaged, grub eaten, field & storage mould Of Which <b>Poor Colour</b> (Aschocyta)	% Max by weight	<b>TDG</b>	6.0%	6.0%	10.0%	10.0%
		<b>DG</b>	3.0%	3.0%	Of Which	Of Which
		<b>PC</b>	3.0%	3.0%	7.0%	7.0%
<b>Foreign material</b> Of Which <b>Unmillable Matter</b> Of Which <b>Soil</b>	% Max by weight	<b>TF</b>	3.0			
		<b>SA</b>	0.5			
		<b>EA</b>	0.3			
<b>Stones</b>	Count	<b>SE</b>	Stones are part of soil. Record the number - it does not matter how many but ensure they do not exceed the 0.3% tolerance for soil			
<b>Snails – Round or Conical</b>	Count in 400 grams	<b>SNR/SNC</b>	2 dead or alive			
<b>Field Insects</b>			30 maximum per 400 grams dead or alive			
<b>Ryegrass Ergot</b>			4cm maximum, pieces laid end to end			

<b>WEED SEED CONTAMINANTS</b> Count per <b>400 Grams</b> *Type 1 individual seed basis			<b>Code</b>	<b>Count</b>
<b>Type 1</b>	Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy (Horned), Wild Poppy		<b>S1*</b>	8
<b>Type 2</b>	Castor Oil Plant, Coriander, Crow Garlic / Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort		<b>S2</b>	NIL
<b>Type 3(a)</b>	Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple		<b>3A</b>	2
<b>Type 3(b)</b>	Vetch (tare and commercial)		<b>3B</b>	4
<b>Type 3(c)</b>	Heliotrope (blue and common)		<b>3C</b>	8
<b>Type 4</b>	Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent (Melilotus) <sup>†</sup> , Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle		<b>S4</b>	20
<b>Type 5</b>	Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea		<b>S5</b>	40
<b>Type 6</b>	Colombus Grass, Johnson, Grass, Saffron Thistle, Clover (Pods), Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Wild Radish (Pods), Trefoil (Pods) <b>(Pods refer to whole pods or part thereof)</b>		<b>S6</b>	10
<b>Type 7(a)</b>	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean		<b>7A</b>	20
<b>Type 7(b)</b>	Barley(2 row), Barley (6 row), Bindweed (Australian), Bindweed (Black), Durum, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum (Grain), Triticale, Turnip Weed, Wheat		<b>7B</b>	20
<b>Type 7(c)</b>	Safflower, Sunflower		<b>7C</b>	2
<b>Type 8</b>	Bellvine		<b>S8</b>	200
<b>Small Foreign Seeds</b>	See CCM section 9 for complete list	% max by weight	<b>SS</b>	0.6
<b>Objectionable Material</b>	Free from animal excreta, rodents (live or dead), live stored product insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds / seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour not normally associated with that pulse and toxic and / or noxious weed seeds prohibited by state laws against inclusion in stockfeed.		NIL	

<sup>†</sup> Hexham scent may only be received if there is no discernible tainting odour imparted on the grain