

	<b>1327</b> VERSION 1	<b>RECEIVAL STANDARDS FOR PEAS &amp; CHICKPEAS</b>			<b>2007/2008 SEASON</b>
	DOCUMENT DATE	1/10/07	OWNER	APPLICATION	

The following standards apply for the receipt of Field Peas

- For details regarding the receipt standards for all pulses refer to the ABA Commodity Classification Manual
- Refer Commodity Classification Manual for Weed Seed Limits
- The Field Peas shall be hard & well filled

Grade	PEAS	PEAW
Grade description	Field Peas	White Peas

Test category	Test Code		
<b>Moisture</b>	% Max	<b>MO</b>	14.0
	<b>Instrument Conversion</b>		
			<b>Kett</b>
			<b>Pea</b>
<b>Purity</b>	% Min by weight		97.0
<b>Defective Material</b>		<b>DG</b>	7.0
Of Which			
<b>Poor Colour</b>	% Max by weight	<b>PC</b>	N/A
Of Which			
<b>Visible Ascochyta</b>		<b>AB</b>	N/A
<b>Foreign Material</b>		<b>TF</b>	3.0
Of Which			
<b>Unmillable Matter</b>	% Max by weight	<b>SA</b>	0.5
Of Which			
<b>Soil</b>		<b>EA</b>	0.3
<b>Stones</b>	Count	<b>SE</b>	Stones are part of soil. Record the number - it does not matter how many but ensure they do not exceed the 0.3% tolerance for soil.
<b>Snails - Dead or Alive</b>			
Round	Count from 200 grams	<b>SN</b>	1
Conical			
<b>Field insects</b>	Count from 200 grams	<b>FI</b>	15 Dead or Alive
<b>Ryegrass Ergot</b>	Count from 200 grams		2cm Max. pieces laid end to end

Weed Seed Contaminants Count Per 200 Grams – Type 1 Individual Seed Basis

		Code	Count
<b>Type 1</b>	Colocynth, Horned Poppy, Jute, Long Headed Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Three Cornered Jack, , Wild Poppy, Poppy (Field)	<b>S1</b>	4
<b>Type 2</b>	Castor Oil Plant, Coriander, Crow Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort, Wild Garlic	<b>S2</b>	NIL
<b>Type 3(a)</b>	Bathurst Burr, Caltrop, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple	<b>3A</b>	1
<b>Type 3(b)</b>	Vetch (tare and commercial)	<b>3B</b>	2
<b>Type 3(c)</b>	Heliotrope (blue and common)	<b>3C</b>	4
<b>Type 4</b>	Bindweed (Field), Cutleaf Mignonette, Darnel, Hoary Cress, #Hexham Scent (Melilotus), Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle	<b>S4</b>	10
<b>Type 5</b>	Creeping Knapweed, Russian Knapweed, Salvation Jane, Sesbania Pea	<b>S5</b>	20
<b>Type 6</b>	Clover (Pods), Columbus Grass, Johnson Grass, Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Saffron Thistle, Trefoil (Pods), Wild Radish (Pods) <b>(Pods refer to whole pods or part thereof)</b>	<b>S6</b>	5
<b>Type 7(a)</b>	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize Soybean, Peas (Field)	<b>7A</b>	10
<b>Type 7(b)</b>	Barley, Bifora, Bindweed (Aust) (Black), Brome grass, Cereal Rye, Mallow, Oats, Oats (Wild), Threehorn Bedstraw, Triticale, Turnip weed, Wheat	<b>7B</b>	10
<b>Type 7(c)</b>	Safflower, Sunflower	<b>7C</b>	1
<b>Type 8</b>	Bellvine	<b>S8</b>	100
<b>Small Foreign Seeds</b>	Canola, Clover Seed, Dock, Lucerne Seed, Medic Seed, Phalaris, Ryegrass, Sow Thistle, Wild Turnip, Wireweed, Yellow Burrweed.	% Max by weight	<b>SS</b> 0.6
<b>Objectionable Material</b>	Free from animal excreta, rodents, live insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds/ seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour not normally associated with that pulse.		NIL

# Hexham sent may only be received if there is no discernible tainting odour imparted on the grain