

Canola Receival Standards Season 2006/2007

Grade	Moisture	Test weight	Foreign material By weight	Wild turnip By count	Broken seeds By count	Total defective	OF WHICH	Damaged seeds (bin burnt, frosted, weather damaged) By Count	Sprouted seeds By count
TEST CODE	MO	TW	TF	WT	BK	DG*		DS	SP
CANO	Max 8.0%	Min 62	Max 3.0%	Max 3.0%	Max 7.0%	Max 8.0%		Max 3.0%	Max 5.0%
CAN 2 [♦]	Max 8.0%	Min 62	Max 3.0%	Max 3.0%	Max 7.0%	Max 10.0%		Max 5.0%	Max 5.0%

*Total Defective is the addition of Damaged Seeds and Sprouted Seeds

♦CAN2 segregation to be implemented only when required

Assessment for Stones / Snails above a 3.0mm screen are to be classified as follows - If one snail / stone is found in the ½ litre sample, then a further four ½ litre samples are to be taken. If 1 snail / stone is found in any one of the subsequent samples, then the load is rejected.

There is a tolerance of 1 stone / snail per ½ litre sample, passing through a 3.0mm round hole screen.

Restricted Seed Contaminants (Limit per 1/2 litre Sample)	Nil Tolerance Seed Contaminants Any other Tainting Agents, or contaminant imparting an objectionable odour	Field Insects Count Per 1/2 litre Sample)	Other Tolerances.
--	---	--	-------------------

Burrs (Xanthium Spp)	1	Jute	3	Alligator Weed	Parthenium Weed	Small Insects	100	Ryegrass Ergot	0.5 cm
Common Heliotrope	3	Thornapple	2	Cape Tulip	Ragweed	Large Insects	10		
Crow Garlic	2	Nightshade	3	Castor Oil Plant	Rattlepod				
Sesbania Pea	65	Wild Mignonette	1	Creeping Knapweed	Saffron Thistle				
Skeleton Weed	2			Coriander	Star Burr				
Hexham Scent	3			Darling Pea	Stinkwort				
Mexican Poppy	3			Dodder	St Johns Wort				
Darnel	3			Giant Sensitive Plant					
Mint Weed	3			Opium Poppy					