

Faba Beans Receival Standards Season 2008/2009

- The following standards apply for the receival of Faba Beans
- For details of definitions used for all pulses refer to the ABB Commodity Classification Manual, including Weed Seed Limits
- Faba Beans shall be, sound, dry, fresh and light to medium brown or pale green in colour
- Sample size 400 grams

Screen Size 3.75mm slotted	Grade		FAB1	FIE1	FAB2	FIE2
	Grade description		Australian No 1 Grade Faba Beans	Australian No 1 Grade Faba Beans	Australian Faba Beans	Australian Fiesta Faba Beans
	Variety		All Except Icarus	Fiesta Manafest Farah, Nura	All Except Icarus	Fiesta Manafest Farah, Nura
Test Category			Test Code			
Moisture	% Max	MO	14.0			
	Instrument Conversion		Kett			
			Faba Bean			
Purity	% Min by weight		97.0			
Total Defective Seeds		TDG	6.0%	6.0%	10.0%	10.0%
Of Which Defective Includes broken, damaged, grub eaten, field & storage mould	% Max by weight	DG	3.0%	3.0%	Of Which	Of Which
Of Which Poor Colour (Aschocyta)		PC	3.0%	3.0%	7.0%	7.0%
Mould (Field or Storage)			NIL			
Foreign material		TF	3.0			
Of Which Unmillable Matter	% Max by weight	SA	0.5			
Of Which Soil		EA	0.3			
Stones	Count	SE	Stones are part of soil. Record the number - it does not matter how many but ensure they do not exceed the 0.3% tolerance for soil			
Snails – Round or Conical	Count in 400 grams	SNR/SNC	2 dead or alive			
Field Insects	30 maximum per 400 grams dead or alive					
Ryegrass Ergot	4cm maximum, pieces laid end to end					

WEED SEED CONTAMINANTS Count per 400 Grams *Type 1 individual seed basis

		Code	Count
Type 1	Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy (Horned), Wild Poppy	S1*	8
Type 2	Castor Oil Plant, Coriander, Crow Garlic / Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort	S2	NIL
Type 3(a)	Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple	3A	2
Type 3(b)	Vetch (tare and commercial)	3B	4
Type 3(c)	Heliotrope (blue and common)	3C	8
Type 4	Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent (Melilotus) [†] , Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle	S4	20
Type 5	Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea	S5	40
Type 6	Colombus Grass, Johnson, Grass, Saffron Thistle, Clover (Pods), Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Wild Radish (Pods), Trefoil (Pods) (Pods refer to whole pods or part thereof)	S6	10
Type 7(a)	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean	7A	20
Type 7(b)	Barley(2 row), Barley (6 row), Bindweed (Australian), Bindweed (Black), Durum, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum (Grain), Triticale, Turnip Weed, Wheat	7B	20
Type 7(c)	Safflower, Sunflower	7C	2
Type 8	Bellvine	S8	200
Small Foreign Seeds	See CCM section 9 for complete list	% max by weight	0.6
Objectionable Material	Free from animal excreta, rodents (live or dead), live stored product insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds / seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour not normally associated with that pulse and toxic and / or noxious weed seeds prohibited by state laws against inclusion in stockfeed.	NIL	

[†] Hexham scent may only be received if there is no discernible tainting odour imparted on the grain