

# Field Pea Receival Standards Season 2008/2009

The following standards apply for the receival of Field Peas

- For details regarding the receival standards for all pulses refer to the ABB Commodity Classification Manual
- The Field Peas shall be hard & well filled
- Sample Size is 200 grams

Screen Size 3.75 mm Slotted	Grade		PEAS	PEAK	PEAW
	Grade description		Field Peas	Kaspa Peas	White Peas
<b>Test Category</b>		<b>Test Code</b>			
<b>Moisture</b>	% Max	<b>MO</b>	14.0		
	<b>Instrument Conversion</b>		<b>Kett Pea</b>		
<b>Purity</b>	% Min by weight		97.0		
<b>Defective Material</b>	% Max by weight	<b>DG</b>	7.0		
<b>Mould (Field or Storage )</b>			NIL		
<b>Foreign Material</b>	% Max by weight	<b>TF</b>	3.0		
Of Which <b>Unmillable Matter</b>		<b>SA</b>	0.5		
Of Which <b>Soil</b>		<b>EA</b>	0.3		
<b>Stones</b>	Count	<b>SE</b>	Stones are part of soil. Record the number - it does not matter how many but ensure they do not exceed the 0.3% tolerance for soil.		
<b>Snails – Round or Conical</b>	Count from 200 grams	<b>SNR/SNC</b>	1 dead or alive		
<b>Field Insects</b>			15 maximum per 200 grams dead or alive		
<b>Ryegrass Ergot</b>			2cm maximum, pieces laid end to end		

Weed Seed Contaminants Count per 200 Grams		*Type 1 Individual Seed Basis	Code	Count	
<b>Type 1*</b>	Colocynth, Double Gees/Three Cornered Jack, Jute, Long Head Poppy, Mexican Poppy, New Zealand Spinach, Parthenium Weed, Poppy (Field), Poppy (Horned), Wild Poppy		<b>S1*</b>	4	
<b>Type 2</b>	Castor Oil Plant, Coriander, Crow Garlic / Wild Garlic, Darling Pea, Opium Poppy, Ragweed, Rattlepods, Starburr, St. Johns Wort		<b>S2</b>	NIL	
<b>Type 3(a)</b>	Bathurst Burr, Caltrop/Cats head/Bulls head, Cape Tulip, Cottonseed, Dodder, Noogoora Burr, Thornapple		<b>3A</b>	1	
<b>Type 3(b)</b>	Vetch (tare and commercial)		<b>3B</b>	2	
<b>Type 3(c)</b>	Heliotrope (blue and common)		<b>3C</b>	4	
<b>Type 4</b>	Bindweed (Field), Cutleaf Mignonette, Darnel (Drake seed), Hexham Scent (Melilotus) <sup>†</sup> , Hoary Cress, Mintweed, Nightshades, Paddy Melon, Skeleton Weed, Variegated Thistle		<b>S4</b>	10	
<b>Type 5</b>	Knapweed (Creeping), Knapweed (Russian), Salvation Jane/Pattersons Curse, Sesbania Pea		<b>S5</b>	20	
<b>Type 6</b>	Colombus Grass, Johnson, Grass, Saffron Thistle, Clover (Pods), Lucerne (Pods), Marshmallow (Pods), Medic (Pods), Muskweed (Pods), Wild Radish (Pods), Trefoil (Pods) <b>(Pods refer to whole pods or part thereof)</b>		<b>S6</b>	5	
<b>Type 7(a)</b>	Chickpeas, Corn, Cowpea, Faba Beans, Lentils, Lupin, Maize (where applicable), Peas (Field), Soybean		<b>7A</b>	10	
<b>Type 7(b)</b>	Barley(2 row), Barley (6 row), Bindweed (Australian), Bindweed (Black), Durum, Oats (Black or Wild), Oats (Sand), Oats (Common), Rice, Rye (Cereal), Sorghum (Grain), Triticale, Turnip Weed, Wheat		<b>7B</b>	10	
<b>Type 7(c)</b>	Safflower, Sunflower		<b>7C</b>	1	
<b>Type 8</b>	Bellvine		<b>S8</b>	100	
<b>Small Foreign Seeds</b>	See CCM section 9 for complete list		% Max by weight	<b>SS</b>	0.6
<b>Objectionable Material</b>	Free from animal excreta, rodents (live or dead), live stored product insect pests, any chemical not registered for use on stored pulses or in excess of legal tolerances, pickling compounds / seed dressings or any fungicide added to the pulse as a seed dressing and any tainting agents and / or contaminants imparting an odour not normally associated with that pulse and toxic and / or noxious weed seeds prohibited by state laws against inclusion in stockfeed.			<b>NIL</b>	

<sup>†</sup> Hexham scent may only be received if there is no discernible tainting odour imparted on the grain