

Canola Receival Standards Season 2007/2008

Grade	Moisture	Test weight	Impurites By weight	OF	Wild turnip By count (500 seeds)	Split Canola seeds By count	Total defective	OF	Damaged seeds: bin burnt, weather damage (not frosted)	Sprouted seeds By count
TEST CODE	MO	TW	IM	WHICH	WT	CS	DG*	WHICH	DS	SP
CANO	Max 8.0%	Min 62	Max 3.0%		Max 3.0%	Max 7.0%	Max 8.0%		Max 3.0%	Max 5.0%
CAN 2*	Max 8.0%	Min 62	Max 3.0%		Max 3.0%	Max 7.0%	Max 10.0%		Max 5.0%	Max 5.0%

*Total Defective is the addition of Damaged Seeds and Sprouted Seeds

◆CAN2 segregation to be implemented only when required

Assessment for Stones / Snails above a 3.0mm screen are to be classified as follows - If one snail / stone is found in the ½ litre sample, then a further four ½ litre samples are to be taken. If 1 snail / stone is found in any one of the subsequent samples, then the load is rejected.

There is a tolerance of 1 stone / snail per ½ litre sample, passing through a 3.0mm round hole screen.

Restricted Seed Contaminants (Limit per 1/2 litre Sample)	Nil Tolerance Seed Contaminants Any other Tainting Agents, or contaminant imparting an objectionable odour	Field Insects (Count Per 1/2 litre Sample)	Other Tolerances.
---	---	--	--------------------------

Burrs (Xanthium Spp)	1	Jute	3	Alligator Weed	Parthenium Weed	Small Insects	100	Ryegrass Ergot	0.5 cm
Common Heliotrope	3	Thornapple	2	Cape Tulip	Ragweed	Large Insects	10		
Crow Garlic	2	Nightshade	3	Castor Oil Plant	Rattlepod				
Sesbania Pea	65	Wild Mignonette	1	Creeping Knapweed	Saffron Thistle				
Skeleton Weed	2			Coriander	Star Burr				
Hexham Scent	3			Darling Pea	Stinkwort				
Mexican Poppy	3			Dodder	St Johns Wort				
Darnel	3			Giant Sensitive Plant					
Mint Weed	3			Opium Poppy					