

	1726 VERSION 1	RECEIVAL STANDARDS FOR MILLING OATS			2008 / 2009 SEASON
	DOCUMENT DATE	20/08/08	OWNER COM	APPLICATION	

PARAMETER		BINNED GRADE		
Test	Test Code	Method	Milling Oat no 1	Possum Milling Oat no. 1
			Grade code	
			MOAT	OATP
Variety	VR		Echidna, Euro, Swan, Dalyup, Mortlock, West, Murray, Pallinup, Possum	POSSUM
Moisture	MO	(Max %)	12.5	12.5
Test weight	TW	Kg/hl min	51.0	52.0
Total impurities		Max % by weight	NA	NA
Of Which				
Screenings - below the 2.0mm slotted screen	SC	Max % by weight	10.0	8.0
Unmillable Above	SA	Max % by weight	NA	NA
Total Foreign	TF	Max % by weight	NA	2.0
Other Oat Varieties	VA	Max % by weight	10	10
Defective Grains				
Damaged Grains	DS	Max % by 200 grains	2.0	2.0
Weather stained grains	WS	Max % by 200 grains	5.0	5.0
Weather stained kernels	WK	Max % by 200 grains	NIL	NIL
Field Fungi		Max % by 200 grains	NIL	NIL
Dry Green/Sappy Green	GO	Max % by 200 grains	5.0	5.0
Frost Damaged	FR	Max % by 200 grains	1	1
Insect Damage	ID	Max % by 200 grains	1	1
Sprouted Grain				
• Early	SP	Max % by 200 grains	NIL	NIL
• Advanced	SH			
Seed Contaminants – * Individual seed basis – Note: Refer to Form 1255 (Wheat Seed Contaminant Types)				
Type 1*	S1*	Max per ½litre	5 NIL for 3 corner jacks	5 NIL for 3 corner jacks
Type 2	S2	Max per ½litre	NIL	NIL
Type 3a	3A	Max per ½litre	NIL	NIL
Type 3b	3B	Max per ½litre	4	4
Type 3c	3C	Max per ½litre	4	4
Type 4	S4	Max per ½litre	10	10
Type 5	S5	Max per ½litre	40	40
Type 6	S6	Max per ½litre	5	5
Type 7	S7	Max per ½litre	1	1
Type 8	S8	Max per ½litre	50 Max 5 Black / Wild Oats	50 Max 10 Black / Wild Oats
Small Foreign Seeds	SS	Max% by weight	0.5%	0.5%
Other Contaminants				
NIL Tolerance for Objectionable Matter, Heat Damaged, Bin Burnt, Pickled or Coloured grain, Odours, Sour Musty or Post Harvest Mouldy Grain and Chemical Residues.				
Smuts / Cereal Ergot		Max count per 1/2 litre	NIL	NIL
Ryegrass Ergot	RE	Max length	2 cm	2cm
Snails Round	SNR	Max count per 1/2 litre	2	2
Conical	SNC			
Stored Grain Insects (Includes Peas Weevil)		Max count per 1/2 litre		
• Alive	LI		Nil	Nil
• Dead	DI		5	5
Field – Live/Dead	FI	Max count per 1/2 litre	3	3
Sitonia Weevil	SI	Max count per 1/2 litre	10	10
Sand - Grains	ES	Max count per 1/2 litre	50	50
Earth – Pea size pieces	EA	Max count per 1/2 litre	3	3